



SAFETY SYSTEM®
YOUR PROTECTOR

Sir Safety System S.p.A. Single-member company
Wholly-owned subsidiary of Sir Holding Srl
Via dei Fornaciai, 9 - Santa Maria degli Angeli
06081 Assisi - Perugia - Italy
Tel.+39 075.8043737 - Fax +39 075.8048686

VAT Nr. IT 03359340548
Viale Europa 74
20090 Cusago Milano
Tel. +39 02.90394575
Fax +39 02.90394441

TECHNICAL SHEET

export@sirsafety.com
www.sirsafety.com



UNI EN ISO 9001:2015
UNI EN ISO 14001:2015

Name: STRATO HELMET WHITE	Code: FD2159	FD21 FALL ARREST DEVICES - PETZL
----------------------------------	---------------------	---

Description

Lightweight helmet suitable for work at a height. The closed outer shell protects from electrical hazards, molten metal and flames. The deformation of the expanded polystyrene inner shell ensures impact resistant properties. The adjustable Centerfit System provides an optimal balance on the head, for better stability. Head circumference: 53-63 cm Weight: 350 g

- The helmet features:
- Side slots for mounting hearing protection.
 - Possible application of protective face shield.
 - Slot for mounting headlamp.
 - Four positioning hooks for mounting a headlamp with an elastic band.
 - Chinstrap designed to decrease the risk of losing the helmet in case of a fall (breaking strength greater than 50 daN).

Features protection against Lateral Deformation LD and Molten Metal splash MM; 440V a.c. Electrical insulation; suitable for temperatures down to -10°C.

The product has been designed and manufactured to comply with Regulation (EU) 2016/425 and subsequent amendments.



Category III	Colours	Available Sizes U
Quantity/Carton 1	EC Standards EN 397 EN 12492 EN 50365	Important Information To be used in conjunction with the other work-positioning devices in confined spaces. Read carefully the user sheet included. Make sure the item is in good condition, undamaged before use. Once you become aware of a damage, you should immediately replace it. Keep in a cool dry place, far from heat sources. Clean the shell with warm soapy water, then rinse with clear water. Do not use any solvents.
Dexterity		Storage and cleaning